info@lenntech.com www.lenntech.com Tel. +31-15-261.09.00



Fax. +31-15-261.62.89 Ultipleat® P-Nylon Filter



Description

The Ultipleat P-Nylon filter is recommended specifically for bulk filtration of photoresists, solvents, TMAH-based developers and other chemicals, that are compatible with nylon 6,6 and High Density Polyethylene (HDPE). The filter design incorporates the latest advance in Pall filtration technology: the crescent shaped Ultipleat® filter configuration.

- · Naturally hydrophilic · Quick venting • Wide range of configurations
- · High flow rates · Integrity testable • Low extractables • Manufactured in a cleanroom environment
- 100% integrity tested

Specifications

Materials

- Medium: Hydrophilic nylon 6,6
- · Core, cage, and end caps: High Density Polyethylene (HDPE)
- · Support and drainage: High Density Polyethylene (HDPE)
- O-ring options: Viton¹ and Teflon¹ encapsulated Viton

Removal Ratings

• 0.1 µm, 40 nm, 20 nm

Filter Areas

- 0.1 μm UNI: 0.93 m^2 / 10 ft^2 per 10 in
- 40 nm UND: 1.2 m² / 13 ft² per 10 in
- 20 nm UNM: 1.4 m² / 15 ft² per 10 in

Configurations

- Nominal length: 254 mm / 10 in, 508 mm / 20 in, 762 mm / 30 in, and 1016 mm / 40 in
- Diameter: 70 mm / 2.75 in
- O-ring size / end caps:

Code 3: 222 double O-ring / flat end Code 8: 222 double O-ring / finned

Code 7: 226 double O-ring bayonet lock / finned end

MR Code 3: 222 double O-ring / flat end designed to retrofit Code 0

elements


Operating Conditions


- Maximum operating temperature: 50°C / 120°F
- · Maximum forward / reverse differential pressure: 275 kPa @ 20°C / 40 psid @ 68°F

Recommended Applications

- Anti-reflective coatings
- Up to 3% TMAH-based developers
- i-line, 248 nm, and 193 nm photoresists
- Solvents
- ¹ Viton and Teflon are registered trademarks of E. I. du Pont de Nemours and Company

Pressure Drop vs. Liquid Flow Rate²





Part Numbers / Ordering Information

| Part Number ³ | Removal Rating | Nominal Length (mm / in) | Configuration Code | O-Ring Material ⁴ |
|-----------------------------|-------------------|-----------------------------|-----------------------|---------------------------------|
| ABD1UNI3EH1 | 0.1 μm | 254 / 10 | 3 | Teflon encapsulated Viton |
| ABD1UNI8EH1 | 0.1 µm | 254 / 10 | 8 | Teflon encapsulated Viton |
| MRD1UNI3EH1 | 0.1 µm | 254 / 10 | 3 | Teflon encapsulated Viton |
| ABD1UND3EH1 | 40 nm | 254 / 10 | 3 | Teflon encapsulated Viton |
| ABD1UND8EH1 | 40 nm | 254 / 10 | 8 | Teflon encapsulated Viton |
| ABD1UNM3EH1 | 20 nm | 254 / 10 | 3 | Teflon encapsulated Viton |
| ABD1UNM8EH1 | 20 nm | 254 / 10 | 8 | Teflon encapsulated Viton |

 $^{^3}$ The above filter configurations are also available in 508 mm / 20 in, 762 mm / 30 in, and 1016 mm / 40 in lengths. These can be ordered by changing the fourth digit in the part number to a 2, 3, or 4 respectively.

Unit conversion: 1 bar = 100 kilopascals

LENNTECH

info@lenntech.com www.lenntech.com Tel. +31-15-261.09.00 Fax. +31-15-261.62.89 Pall Corporation has offices and plants throughout the world.

E91b 12/07

 $^{^{\}rm 2}$ For liquids with a viscosity differing from water, multiply the pressure drop by the viscosity in centipoise.

⁴ Other Ö-ring materials are available.

[©] Copyright 2007 Pall Corporation. Pall. All Ultipleat are trademarks of Pall Corporation. © Indicates a Pall trademark registered in the USA. Filtration. Separation. Solution.sm is a service mark of Pall Corporation.