# LENNTECH

info@lenntech.com www.lenntech.com

Tel. +31-15-261.09.00

Fax. +31-15-261.62.89




### Pall Schumasiv<sup>®</sup> Ceramic Membrane Filter Elements

#### Description

Pall<sup>®</sup> ceramic membrane filter elements are made of pure  $\alpha$  Al<sub>2</sub>O<sub>3</sub>, the chemical stable variant of alumina and the membranes consist of Al<sub>2</sub>O<sub>3</sub>, ZrO<sub>2</sub> or TiO<sub>2</sub>, depending on pore size.

Due to fine nuanced manufacturing steps, **Schumasiv** ceramic membrane filter elements can be produced with a wide range of pore sizes covering the whole range of micro and ultra filtration. The tube shaped mono and multi channel filter elements are suitable for applications under abrasive and chemical aggressive conditions. **Schumasiv** filter elements have an outstanding filtration efficiency at high flux rates, e.g. on oil / water separation applications.



#### **Applications**

#### Membranes

<ul> <li>Chemical Industry</li> </ul>	Process water, acid and lye				
	filtration, catalytic recovery				
Oil / Water Separation	Compressor condensate filtration,				
	degreasing baths, washing water,				
	coolant lubricants				
Waste Water	Biomass separation,				
	COD reduction				
Food and Beverage Industry	Various applications				
	for clarification				

#### **Technical Information**

• Support	$\alpha$ -Al <sub>2</sub> O <sub>3</sub>
Membranes	
Microfiltration	$\alpha$ -Al <sub>2</sub> O <sub>3</sub> : 2 to 0.2 $\mu$ m
Ultrafiltration	$ZrO_2$ or $TiO_2$ : 0.1 to 0.005 $\mu$ m
Maximum Pressure	15 bar
• Maximum Temperature	
Epoxy resin sealing	120 °C
PTFE sealing	200 °C
Porosity (support)	Approximately 33 %

### Chemical Resistance<sup>1</sup>

Schumasiv filter elements are resistant against most chemicals. Care should be taken when operating continuously with high acid concentrations at elevated temperatures. Schumasiv filter elements are not resistant against HF.

Resistance of Epoxy resin against strong acids and polar organic substances like short-chained carboxylic acids and alcohols is limited.

<sup>1</sup> As end use conditions can vary, it is the users responsibility to verify compatibility with their specific use conditions.

#### **General Information**

- Module housings are manufactured from stainless steel and are available for all geometries.
- Module housings can be supplied containing up to 28 m<sup>2</sup> of membrane surface area.
- All connection variations are possible.

#### **Ordering Information**

Schumasiv (MF)	Unit	01/7	01/16	07/6	19/3.3	31/2.8	19/6	37/3.6	61/3.1	19/8
Number of Channels		1	1	7	19	31	19	37	61	19
Channel Diameter	mm	7	16	6	3.3	2.8	6	3.6	3.1	8
Outer Diameter	mm	10	25.4	25.4	25.4	25.4	41	41	41	52
Membrane Surface 1	m <sup>2</sup>	0.022	0.050	0.132	0.200	0.292	0.358	0.418	0.352	0.478
Length <sup>2</sup>	mm	1000	1000	1000	1000	1200	1000	1000	1200	1000
Part Number for										
1.2 µm Membrane	mm	88501101	89582262	89582267	88519151		88519810 <sup>3</sup>	88537091		89580914 <sup>3</sup>
Part Number for 0.6 µm Membrane	mm	88501091	89582263	89582268	88519311	89581045 0.8 μm	88519611	88537071	89581006 0.8 μm	89580370
Part Number for										
0.2 µm Membrane	mm	88501041	89582264	89582269	88519001	89580973	88519021	88537011	89580975	88519401
Part Number for 0.05 µm Membrane	mm	88501051	89582265	89582270	88519041	89580972	88519101	88537001	89580974	88519391
Part Number for 0.005 µm Membrane	mm	88501061	89582266	89582271	88519081	89581046	88519421	88537111	89581042	88519491

<sup>1</sup> at 1000 mm length.

<sup>2</sup> standard length, 1200 mm possible, other dimensions upon request.

<sup>3</sup> end sealing with Epoxy resin (all others with PTFE sealing).

## LENNTECH

info@lenntech.com www.lenntech.com Tel. +31-15-261.09.00 Fax. +31-15-261.62.89 Pall Corporation has offices and plants throughout the world. For Pall representatives in your area, please go to www.pall.com/corporate\_contact.asp

Please contact Pall Corporation for product applicability to specific National legislation and/or Regional Regulatory requirements for water and food contact use.

Because of technological developments related to the products, systems, and/or services described herein, the data and procedures are subject to change without notice. Please consult your Pall representative or visit www.pall.com to verify that this information remains valid.

© Copyright 2008, Pall Corporation. Pall, \* Indicates a trademark registered in the USA. Filtration. Separation. Solution. зм is a service mark of Pall Corporation.